



UPPER CUT

ELECTRONIC CONTACT CLEANER







DESCRIPTION

UPPER CUT is a high purity, high dielectric, rapidly evaporating, non-flammable aerosol spray contact and circuit board cleaner. Specially formulated for removing condensation, dust and other particulate matter from sensitive electronic parts. Quick drying formula will not harm most plastics, paints or rubbers. This solvent system has tested safe on Neoprene, Buna, Silicone, Butyl and Natural Rubber, Nylon, Hypalon®, PTFE, PVC, Polyurethane, Polyethylene, Polypropylene, Epoxy and ABS.

APPLICATIONS

This contact cleaner is great for use on circuit boards, wire terminals, relays, switches, contacts, circuit breakers, tuners, potentiometers, and control panels.

FEATURES & BENEFITS

- Evaporates Quickly Leaving No Residue
- Safe on Most Plastics
- · EPA SNAP Approved

- Non-Flammable & Non-Corrosive
- · 30,000 Volt Dielectric Strength

SPECIFICATIONS

FORM: Solvent-Based Aerosol ODOR: Solvent COLOR: Colorless DETERGENCY: None TOXICITY: 200 ppm WETTING ABILITY: Saturates STORAGE STABILITY: 1 Year COLD STABILITY: 0°F

PHOSPHATES: None

FLASH POINT: N/A
FLAME EXTENSION: N/A
SOLUBILITY IN WATER: Non-soluble
SPECIFIC GRAVITY: 1.25
% VOC: 74.9
pH: N/A
VISCOSITY: Thin
EVAPORATION RATE: Fast

BIODEGRADABILITY: No

LABEL INFORMATION

UPPER CUT ELECTRONIC CONTACT CLEANER

A high purity, high dielectric, rapidly evaporating, non-flammable aerosol spray contact and circuit board cleaner. Specially formulated for removing condensation, dust and other particulate matter from sensitive electronic parts. Quick drying formula will not harm most plastics, paints or rubbers. This solvent system has tested safe on Neoprene, Buna, Silicone, Butyl and Natural Rubber, Nylon, Hypalon®, PTFE, PVC, Polyurethane, Polyethylene, Polypropylene, Epoxy and ABS.

USE ON: Circuit boards, wire terminals, relays, switches, contacts, circuit breakers, tuners, potentiometers, and control panels.

Not recommended for use on Acrylic or Stressed Polycarbonate materials. Pre-testing is strongly suggested. Zero residue formula is also excellent for cleaning metal parts and fittings. NOTE: If there is any doubt as to the material construction this product is to be used on, test on a small hidden surface prior to general use.


DIRECTIONS: Spray directly onto surface, holding can close to work. For hard to reach areas, insert extension tube into actuator orifice. Allow components to dry completely before applying current.

DANGER: Contains gas under pressure; may explode if heated. Harmful if swallowed. Causes skin and serious eye irritation. May cause drowsiness or dizziness. May be fatal if swallowed and enters airways.

Keep away from heat, sparks, open flames and hot surfaces. -No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. Store in a well-ventilated place. Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. If swallowed: Immediately call a poison center or doctor. Do NOT induce vomiting. Rinse mouth. Wear protective gloves and eye protection. If on skin: Wash with plenty of water. If skin irritation occurs: Get medical advice or attention. Take off contaminated clothing and wash it before reuse. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice or attention. Avoid breathing mist, vapors or spray. Use only outdoors or in a well-ventilated area. If inhaled: Remove person to fresh air and keep comfortable for breathing. Call a poison center or doctor if you feel unwell. Dispose of contents and container in accordance with local, state and federal regulations.

VOC Category: Electronic Cleaner VOC Limit: 75%

CONTAINS (CAS#): Trans-1,2-dichloroethylene, (156-60-5), 1,1,2,2-Tetrafluoroethyl-2,2,2-trifluoroethylether, (406-78-0), Carbon Dioxide, (124-38-9).





PACKAGING INFORMATION